

Fujikura 28S

NEW

Features

- Active V-groove Alignment
- Fast splicing time 6sec.
- Touch panel with easy operation
- Simple lightweight carrying case for good mobility



Single Fiber Fusion Splicer

Fujikura 28S

Active V-groove Alignment

SPECIFICATIONS

Applicable fiber	Single / SMF(G.652/657), MMF(G.651), DSF(G.653), NZDSF(G.655)
Cladding dia. / Sheath dia.	125 μm / Up to 3mm with sheath clamp
Cleave length	5mm to 16mm
Splice mode / heating mode	Total 100 splice modes / 30 heating modes
Typical splice loss ^{*1}	0.03dB (SM), 0.01dB(MM), 0.05dB(DS) and 0.05dB(NZDS)
Return loss	>>60dB
Typical splice time	6sec SM FAST, 9sec SM AUTO
Typical tube heating time	25sec FP-03, coating dia.250μm
Splice result storage	Last 10,000 splices
Viewing methods / magnification	2 axis 2CMOS camera with 5.0" color LCD. 132X magnification.200X magnification after splicing
Tension test	1.96 to 2.25N
Applicable protection sleeve	60mm, 40mm and Fujikura micro sleeves
No. of splice / heating per battery full charge	Typical 200 cycles with BTR-11 ^{*2}
Electrode life	Typical 5000 splices
Size / weight	131W x 201D x 79H mm / 1300g (including battery)
Operating condition	Altitude : 0 to 5,000m above sea level, Wind : 15m/sec ^{*3} , Temperature : -10 to 50deg C, Humidity : 0 to 95%RH, non-dew
Resistance feature ^{*4}	Shock resistance : 76cm (30inch) bottom surface drop Dust resistance : Exposure to dust (0.1 to 500μm dia. Alumina Silicate) ,IP5X Rain resistance : H=10mm/hr for 10min ,IPX2
Other features	PC software upgrade / data management
Terminals	USB 2.0 (Mini-B type) connector for PC communication.

^{*1}:Typical value of the inspection with Fujikura identical fiber. Measured by cut-back method relevant to ITU-T and IEC standards.

^{*2}:one(1) splicing and heating cycle per two(2) min. under room temperature condition.

^{*3}:Under strong wind, it is necessary to lengthen the heating time setting.

^{*4}:The shock, dust and rain resistance test do not guarantee the product will not be damaged under these conditions.

Fujikura

Single Fiber Fusion Splicer
Fujikura 28S
Active V-groove Alignment

STANDARD PACKAGE

Description	Model No.	Q'ty
Fusion Splicer	28S	1pc
AC adapter	ADC-19A	1pc
AC Power cord	ACC-11	1pc
Built in battery pack**	BTR-11(Li-ion)**	1pc
Single Fiber Cleaver	CT-08	1pc
Primary/secondary coat stripper	3 in one stripper	1pc
Carrying case	CC-35	1pc
Spare electrodes	ELCT2-16B	1pair
Instruction manual CD	M-31	1pc
Quick reference guide	Q-31S-E	1pc

OPTIONAL ITEMS

Description	Model No.
Fiber holder	FH-60-250 (coating dia. of 250μm)
	FH-60-900 (coating dia. of 900μm)
	FH-60-DC250 (coating dia. of 250μm in drop cable)
	FH-FC-20 (coating dia. of 900μm in 2.0mm Sheath dia.)
	FH-FC-30 (coating dia. of 900μm in 3.0mm Sheath dia.)
	FH-60-LT900 (900μm dia. loose buffer fiber)
Sheathclamp	CLAMP-S31A (included in standard package)
	CLAMP-S31B (900μm dia. loose buffer fiber)

**all senders have to ovey the IATA regulation in case of Li-ion battery transportation by air.

Please visit **NEW** web site!

www.sanjayinfocom.com

Fujikura 28S



NEW

 **twitter**
<https://twitter.com/fujikurasplicer>

Specifications and descriptions are subject to change without prior notice. © 2018 Fujikura Ltd.